

Product data sheet

Characteristics

413QC-WE

SOCKET SURF QUICK CONN 250V10A



Main

Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

Complementary

Colour code	WE
Marking	Without marking
Local signalling	Without light indicator
Device mounting	Surface
Fixing mode	By screws
Material	Plastic
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Network frequency	50 Hz
Depth	46 mm
Length	70 mm
Width	47 mm
Fixing center	50 mm
Number of poles	1

Environment

Standards	AS 3109 AS 3100 AS/NZS 3112
-----------	-----------------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	54.0 g
Package 1 Height	4.8 cm
Package 1 width	5 cm
Package 1 Length	7 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile