

## Product data sheet

### Characteristics

# 414L-WE

Rear Connecting Surface Socket, 250VAC,  
10A, Twin 3 PIN, Round Earth Pin



### Main

Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Outlet standard description	Pin earth
Quantity per set	Set of 1
Cover type	Complete housing

### Complementary

Colour code	WE
Marking	Without marking
Local signalling	Without light indicator
Device mounting	Surface
Fixing mode	By screws
Material	Plastic
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Network frequency	50 Hz
Depth	63 mm
Length	72 mm
Width	65 mm
Fixing center	50 mm
Number of poles	1

### Environment

Standards	AS 3109 AS 3100 AS/NZS 3112
-----------	-----------------------------------

### Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	6.3 cm
Package 1 Width	6.5 cm
Package 1 Length	7.2 cm
Package 1 Weight	0.125 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>