

# Product data sheet

## Characteristics

# 415-WE

## SOCKET FLUSH 3PIN 10A 250V



### Main

Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

### Complementary

Colour code	WE
Marking	Without marking
Local signalling	Without light indicator
Device mounting	Flush
Fixing mode	By screws
Material	PVC (polyvinyl chloride)
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Depth	27 mm
Length	94 mm
Width	42 mm
Fixing center	84 mm

### Environment

Standards	AS/NZS 3112 AS 3100 AS 3109 AS/NZS 3122:approval number S/1
-----------	--

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	58.0 g
Package 1 Height	2.7 cm
Package 1 width	4.2 cm
Package 1 Length	9.4 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	0.51 kg
Package 2 Height	10.2 cm
Package 2 width	11.7 cm
Package 2 Length	13.8 cm
Unit Type of Package 3	CAR

Number of Units in Package 3	100
Package 3 Weight	5.8 kg
Package 3 Height	15.7 cm
Package 3 width	30.5 cm
Package 3 Length	44.5 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>