

Product data sheet

Characteristics

415LB-WE

Socket Flush 3 PIN 10A 250V Lb



Main

Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

Complementary

Colour code	WE
Marking	Without marking
Local signalling	Without light indicator
Device mounting	Flush
Fixing mode	By screws
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Depth	27 mm
Length	94 mm
Width	42 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3112 AS 3100 AS 3109 AS/NZS 3122:approval number S/1
-----------	----------------------------------------------------------------------

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	4 cm
Package 1 Length	6 cm
Package 1 Weight	40 g
Unit Type of Package 2	Gyári csomagolás
Number of Units in Package 2	25
Package 2 Height	8.5 cm
Package 2 Width	14.4 cm
Package 2 Length	17.9 cm
Package 2 Weight	1.1 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	250

Package 3 Height	18.2 cm
Package 3 Width	30.8 cm
Package 3 Length	45.3 cm
Package 3 Weight	11 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile