

Product data sheet

Characteristics

415MP-WE

Standard Series, Single Switch Socket Outlet, Panel Mount, 250VAC, 10A



Main

Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

Complementary

Colour code	WE
Marking	Without marking
Local signalling	Without light indicator
Mounting support	panel
Fixing mode	By screws
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Depth	25 mm
Length	45 mm
Width	42 mm
Number of poles	1

Environment

Standards	AS/NZS 3112 AS 3100 AS 3109 AS/NZS 3122:approval number S/1
-----------	--

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	4.7 cm
Package 1 Length	4.2 cm
Package 1 Weight	42 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	7 cm
Package 2 Width	8.8 cm
Package 2 Length	11.2 cm
Package 2 Weight	0.24 kg
Unit Type of Package 3	CAR

Number of Units in Package 3	50
Package 3 Height	11.7 cm
Package 3 Width	25 cm
Package 3 Length	31 cm
Package 3 Weight	2.9 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile