

Product data sheet

Characteristics

415VF-WE

UNSWITCHED SOCKET OUTLET 10A



Main

Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Full cover plate
Socket additional information	With hinged lid

Complementary

Colour code	WE
Marking	Without marking
Local signalling	Without light indicator
Device mounting	Flush
Fixing mode	By screws
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Depth	38 mm
Length	101 mm
Width	80 mm
Fixing center	76 x 65 mm



Environment

Standards	AS/NZS 3112 AS 3100 AS 3109 AS/NZS 3122:approval number S/1
IP degree of protection	IP34

Packing Units

Package 1 Weight	154.000 g
Package 1 Height	60.000 mm
Package 1 width	78.000 mm
Package 1 Length	110.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
