

Product data sheet

Characteristics

418S-WE

PLG TP SD ENTRY 250V 10A IN.PN



Main

Range of product	Standard Series
Product brand	Clipsal

Complementary

[In] rated current	10 A
[Ue] rated operational voltage	230 V 50/60 Hz conforming to EN 60309-2
Colour	White electric
Material	Plastic
Connections - terminals	Screw terminal
Plug, socket, control station shape	Angled
Duration	6 h

Packing Units

Package 1 Weight	41.800 g
Package 1 Height	40.000 mm
Package 1 width	99.000 mm
Package 1 Length	192.000 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.