

Product data sheet

Characteristics

418S-WE

Standard Series, Plug Top, Side Entry, 3 PIN,
10A, 250V



Main

Range of product	Standard Series
Product brand	Clipsal

Complementary

[In] rated current	10 A
[Ue] rated operational voltage	230 V 50/60 Hz conforming to EN 60309-2
Colour	White electric
Material	Plastic
Connections - terminals	Screw terminal
Plug, socket, control station shape	Angled
Duration	6 h

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.6 cm
Package 1 Width	7.1 cm
Package 1 Length	10.0 cm
Package 1 Weight	42.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations