

## Product data sheet

### Characteristics

# 418S15-WE

## Plug Top, Side Entry, 3 PIN, 15A, 250V



### Main

Range of product	Standard Series
Product brand	Clipsal

### Complementary

[In] rated current	15 A
[Ue] rated operational voltage	230 V 50/60 Hz conforming to EN 60309-2
Colour	White electric
Material	Plastic
Connections - terminals	Screw terminal
Plug, socket, control station shape	Angled
Duration	6 h

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.8 cm
Package 1 Width	7.1 cm
Package 1 Length	9.9 cm
Package 1 Weight	44 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	72 cm
Package 2 Width	98 cm
Package 2 Length	122 cm
Package 2 Weight	0.25 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.