

## Product data sheet

### Characteristics

# 418SUA-BK

## Plug Top, Side Entry, 10A, Unassembled



### Main

Range of product	Standard Series
Product brand	Clipsal

### Complementary

[In] rated current	10 A
[Ue] rated operational voltage	230 V 50/60 Hz conforming to EN 60309-2
Colour	Black
Material	Plastic
Connections - terminals	Screw terminal
Plug, socket, control station shape	Angled
Duration	6 h

### Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	4.5 cm
Package 1 Length	5.5 cm
Package 1 Weight	0.042 kg

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>