

## Product data sheet

### Characteristics

# 41E10PBSWM-VW

## Clipsal Iconic Push Button Wisier Smart Switch Mechanism, 10A, ControlLink, 3 Wire



### Main

Range compatibility	Wiser hub
Product brand	Clipsal
Range	Iconic
Product or component type	Connected switch

### Complementary

Device presentation	Mechanism
Technology type	Electronic
Number of rocker	1
Actuator	Push-button
Load type	Dimmable LED lighting driver: 10 A LED lighting driver (non-dimmable): 10 A Electronic transformer: 10 A Medium voltage halogen lamp: 10 A Linear fluorescent ballast: 10 A Inductive: 6 A (cos phi =0.6) Resistive: 15 A Motor: 10 A
[Ue] rated operational voltage	220...240 V AC 50 Hz
Protection type	Over temperature protection Thermal protection
Colour tint	Vivid white (VW)
Surface finish	Glossy
Local signalling	LED
Control type	Push-button By mobile application Multi-way control via ControlLink
Software name	Wiser App
Maximum number of connected devices	3 (switch) 2 (ControlLink module)
Cable length	50 m for ControlLink module
Technology type	Bluetooth low energy default Zigbee
Communication network type	Wireless (2.4 GHz), 2.5 mW
Memory description	Backup memory - date and time for 6 h Backup memory - program for indefinite period
Wiring configuration	3-wire
Material	Plastic
Mounting support	Grid
Device mounting	Flush
Fixing mode	Clip-in

Fixing center	84 mm
Type of installation	Indoor installation
Embedding depth	70 mm
Depth	56 mm
Width	48 mm
Height	22 mm

## Environment

IP degree of protection	IP20
Relative humidity	5...90 % non-condensing
Standards	AS/NZS 60669.2.1 safety AS/NZS 60669.2.1 EMC AS/NZS 4268 radio

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4 cm
Package 1 Width	7.8 cm
Package 1 Length	9.5 cm
Package 1 Weight	91 g
Unit Type of Package 2	CAR
Number of Units in Package 2	48
Package 2 Height	224 cm
Package 2 Width	261 cm
Package 2 Length	335 cm
Package 2 Weight	5 kg
Package 3 Height	110 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>