

Product data sheet

Characteristics

41E300PBUD2SM-VW

Clipsal Iconic, dimmer, 40M, universal, PB, controlLink, 200 W, Vivid White



Main

Range	Clipsal Iconic
Product or component type	Dimmer
Device presentation	Mechanism
Dimmer type	Universal
Colour tint	Vivid white (VW)
Type of packing	Box
Load type	Dimmable LED - 300 W - 240 V AC Low voltage halogen lamp with iron core transformer - 300 W - 240 V AC Incandescent - 300 W - 240 V AC




Complementary

Range compatibility	Clipsal Iconic
Control type	Push-button ControlLink
Fixing mode	Clip-in
Surface finish	Glossy
Ambient air temperature for storage	0...60 °C
[Ue] rated operational voltage	220...240 V AC 50 Hz
Function available	Brightness adjustment
Protection type	Short-circuit
Ambient air temperature for operation	0...45 °C
Relative humidity	5...90 %
Connections - terminals	Screw terminal
Clamping connection capacity	3 x 1.5 mm ²
Height	23.5 mm
Width	23.5 mm
Depth	41 mm
Embedding depth	39 mm

Packing Units

Package 1 Weight	66.000 g
Package 1 Height	40.000 mm
Package 1 width	65.000 mm
Package 1 Length	85.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration

Environmental Disclosure

 [Product Environmental Profile](#)

Circularity Profile

 [End Of Life Information](#)
