

Product data sheet

Characteristics

41E300PBUD2SM-VW

Clipsal Iconic, dimmer, 40M, universal, PB, controlLink, 200 W, Vivid White



Main

Range	Clipsal Iconic
Product or component type	Dimmer
Device presentation	Mechanism
Dimmer type	Universal
Colour tint	Vivid white (VW)
Type of packing	Box
Load type	Dimmable LED - 300 W - 240 V AC Low voltage halogen lamp with iron core transformer - 300 W - 240 V AC Incandescent - 300 W - 240 V AC

Complementary

Range compatibility	Clipsal Iconic
Control type	Push-button ControlLink
Fixing mode	Clip-in
Surface finish	Glossy
Ambient air temperature for storage	0...60 °C
[Ue] rated operational voltage	220...240 V AC 50 Hz
Function available	Brightness adjustment
Protection type	Short-circuit
Ambient air temperature for operation	0...45 °C
Relative humidity	5...90 %
Connections - terminals	Screw terminal
Clamping connection capacity	3 x 1.5 mm ²
Height	23.5 mm
Width	23.5 mm
Depth	41 mm
Embedding depth	39 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	6.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	68 g
Unit Type of Package 2	BB2
Number of Units in Package 2	6
Package 2 Height	130 cm
Package 2 Width	100 cm
Package 2 Length	154 cm
Package 2 Weight	0.52 kg
Package 3 Height	150 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information