

Product data sheet

Characteristics

41ECSFWMZ-VW

Clipsal Iconic, Connected AC Fan Controller, Zigbee



Main

Product brand	Clipsal
Range	Iconic
Aesthetic name	Iconic Iconic Essence Iconic Styl
Product or component type	Connected switch
Concentrator compatibility	Wiser hub generation 1
Mobile App name	Wiser by SE

Complementary

Device presentation	Mechanism
Technology type	Electronic
Number of rocker	1
Actuator	Push-button
Load type	230 V AC fan: 150 W
[Ue] rated operational voltage	220...240 V AC 50 Hz
Fuse type	220...240 V 50 Hz
Protection type	Over temperature protection Thermal protection
Colour tint	Vivid white (VW)
Number of modules	1 module
Local signalling	Fan speed: 1 LED (amber/green/red)
Signalling function	Fan speed
Control type	OFF-LOW-MEDIUM-HIGH fan speed controller fan speed control By mobile application
Software name	Wiser by SE App: fan control
Maximum number of connected devices	3 (switch)
Technology type	Zigbee default Bluetooth low energy
Communication network type	Wireless (2.4 GHz), 2.5 mW at < 50 m
Memory description	Backup memory - date and time for 6 h Backup memory - program for indefinite period
Material	Plastic
Mounting support	Grid
Device mounting	Flush
Fixing mode	Clip-in
Fixing center	84 mm
Type of installation	Indoor installation
Embedding depth	53 mm
Depth	58 mm
Width	48 mm
Height	22 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Ambient air temperature for operation	-10...50 °C
IP degree of protection	IP20
Relative humidity	5...90 % non-condensing
Standards	AS/NZS 60669.2.1 safety AS/NZS 60669.2.1 EMC AS/NZS 4268 radio

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.2 cm
Package 1 Width	8 cm
Package 1 Length	9.6 cm
Package 1 Weight	72 g
Unit Type of Package 2	PAL
Number of Units in Package 2	2304
Package 2 Height	95 cm
Package 2 Width	114 cm
Package 2 Length	114 cm
Package 2 Weight	289.136 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	48
Package 3 Height	23 cm
Package 3 Width	26.7 cm
Package 3 Length	34.1 cm
Package 3 Weight	4.32 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information