

Product data sheet

Characteristics

42E350RLD2M-VW

Clipsal Iconic, dimmer, 40M, LED, rotary , 350 W, Vivid White



Main

| | |
|---------------------------|--|
| Range | Clipsal Iconic |
| Product or component type | Dimmer |
| Device presentation | Mechanism |
| Dimmer type | Universal |
| Colour tint | Vivid white (VW) |
| Type of packing | Box |
| Load type | Dimmable LED - 350 W - 240 V AC Incandescent - 350 W - 240 V AC Low voltage halogen lamp with electronic transformer - 350 W - 240 V AC Dimmable fluocompact lamp - 150 W - 240 V AC Dimmable fluorescent - 150 W - 240 V AC |

Complementary

| | |
|---------------------------------------|--|
| Range compatibility | Clipsal Iconic |
| Control type | Rotary knob |
| Fixing mode | Clip-in |
| Surface finish | Glossy |
| Ambient air temperature for storage | 0...60 °C |
| Dimmer control | 315° rotary setting |
| [Ie] rated operational current | 1.5 A |
| [Ue] rated operational voltage | 220...240 V AC 50 Hz 1 W |
| Function available | Brightness adjustment |
| Protection type | Short-circuit |
| Ambient air temperature for operation | 0...45 °C |
| Relative humidity | 0...90 % |
| Connections - terminals | Flying leads |
| Local signalling | LED |
| Material | PC (UL94 V-2): top PC MAS056 (UL94 V-2): bottom |
| Height | 22.5 mm |
| Width | 22.5 mm |
| Depth | 39 mm |
| Embedding depth | 37 mm |

Environment

| | |
|-----------------|---|
| Derating factor | 1 deviceswithout derating 2 deviceswith derating factor 3 deviceswith derating factor |
| Standards | AS/NZS 60669.2.1 |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

| | |
|------------------|-----------|
| Package 1 Weight | 59.000 g |
| Package 1 Height | 49.000 mm |
| Package 1 width | 70.000 mm |
| Package 1 Length | 89.000 mm |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End Of Life Information |