

Product data sheet

Characteristics

42E350RLD2M-VW

Clipsal Iconic, dimmer, 40M, LED, rotary , 350 W, Vivid White



Main

Range	Clipsal Iconic
Product or component type	Dimmer
Device presentation	Mechanism
Dimmer type	Universal
Type of packing	Box
Load type	Dimmable LED - 350 W - 240 V AC Incandescent - 350 W - 240 V AC Low voltage halogen lamp with electronic transformer - 350 W - 240 V AC Dimmable fluocompact lamp - 150 W - 240 V AC Dimmable fluorescent - 150 W - 240 V AC

Complementary

Range compatibility	Clipsal Iconic
Control type	Rotary knob
Fixing mode	Clip-in
Surface finish	Glossy
Ambient air temperature for storage	0...60 °C
Dimmer control	315° rotary setting
[Ie] rated operational current	1.5 A
[Ue] rated operational voltage	220...240 V AC 50 Hz 1 W
Function available	Brightness adjustment
Protection type	Short-circuit
Ambient air temperature for operation	0...45 °C
Relative humidity	0...90 %
Connections - terminals	Flying leads
Local signalling	LED
Material	PC (UL94 V-2): top PC MAS056 (UL94 V-2): bottom
Height	22.5 mm
Width	22.5 mm
Depth	39 mm
Embedding depth	37 mm

Environment

Derating factor	1 deviceswithout derating 2 deviceswith derating factor 3 deviceswith derating factor
Standards	AS/NZS 60669.2.1

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	3.2 cm
Package 1 Width	6.2 cm
Package 1 Length	8.4 cm
Package 1 Weight	10 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information