

Product data sheet

Characteristics

435/110-BK

SOCKET INLET 3PN FLUSH 10A 110



Main

Product brand	Clipsal
---------------	---------

Complementary

[In] rated current	10 A
[Ue] rated operational voltage	110 V 50/60 Hz conforming to EN 60309-2
Colour	Body: black
Plug, socket, control station shape	Straight
Service life in hours	4 h

Packing Units

Package 1 Weight	0.092 kg
------------------	----------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.