

Product data sheet

Characteristics

438/110-GY

SOCKET CORD EXTENSION 0.75X1SQ

FLEXIBLE 110V



Main

Range of product	Standard Series
Colour	Grey
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

Complementary

Colour code	GY
Marking	Without marking
Local signalling	Without light indicator
Material	PVC (polyvinyl chloride)
[In] rated current	10 A
[Ue] rated operational voltage	110 V AC
Depth	71 mm
Diameter	43 mm


Environment

Standards	AS/NZS 3112 AS 3100 AS 3109 AS/NZS 3122:approval number S/1
-----------	--

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.7 cm
Package 1 Width	10 cm
Package 1 Length	18.5 cm
Package 1 Weight	60.6 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration

RoHS exemption information

 [Yes](#)

Environmental Disclosure

 [Product Environmental Profile](#)
