

Product data sheet

Characteristics

438/2-TR

Flexible Cord Extension Socket, Standard Series, 125VAC, 10A, 2 PIN ParAllel

Main

Range of product	Standard Series
Product or component type	Socket-outlet
Colour	Transparent
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

Complementary

Colour code	TR
Marking	Without marking
Local signalling	Without light indicator
Material	PVC (polyvinyl chloride)
[In] rated current	10 A
[Ue] rated operational voltage	110 V AC
Depth	71 mm
Diameter	43 mm



Environment

Standards	AS/NZS 3112 AS 3100 AS 3109 AS/NZS 3122:approval number S/1
-----------	--

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.6 cm
Package 1 Width	10 cm
Package 1 Length	4 cm
Package 1 Weight	53.4 g

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes