

Product data sheet

Characteristics

438/32-WE

Standard Series, Flexible Cord Extension

Socket, 32VAC, 10A, 2 PIN ParAllel



Main

Range of product	Standard Series
Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

Complementary

Colour code	WE
Marking	Without marking
Local signalling	Without light indicator
Material	PVC (polyvinyl chloride)
[In] rated current	15 A
[Ue] rated operational voltage	32 V DC
Depth	71 mm
Diameter	43 mm




Environment

Standards	AS/NZS 3112 AS 3100 AS 3109 AS/NZS 3122:approval number S/1
-----------	--

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4 cm
Package 1 Width	7 cm
Package 1 Length	10 cm
Package 1 Weight	49.3 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations