

Product data sheet

Characteristics

438S15-TR

SOCKET W-8MM SHROUD 15A250V



Main

Range of product	Standard Series
Colour	Transparent
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

Complementary

Colour code	TR
Marking	Without marking
Local signalling	Without light indicator
Material	PVC (polyvinyl chloride)
[In] rated current	15 A
[Ue] rated operational voltage	250 V AC
Depth	71 mm
Diameter	43 mm




Environment

Standards	AS/NZS 3112 AS 3100 AS 3109 AS/NZS 3122:approval number S/1
-----------	--

Packing Units

Package 1 Weight	60.000 g
Package 1 Height	50.000 mm
Package 1 width	70.000 mm
Package 1 Length	100.000 mm

Offer Sustainability

EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration