

Product data sheet

Characteristics

438UA-GY

SOCKET CORD EXTENSION 0.75X1SQ FLEXIBLE UA



Main

Range of product	Standard Series
Product or component type	Socket-outlet
Colour	Grey
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

Complementary

Colour code	GY
Marking	Without marking
Local signalling	Without light indicator
Material	PVC (polyvinyl chloride)
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Depth	71 mm
Diameter	43 mm

Environment

Standards	AS/NZS 3112 AS 3100 AS 3109 AS/NZS 3122:approval number S/1
-----------	--

Packing Units

Package 1 Weight	0.059 kg
Package 1 Height	72.000 mm
Package 1 width	50.000 mm
Package 1 Length	50.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile