

## Product data sheet

### Characteristics

# 439S-WE

## PLUG TOP 3 INS. PIN 10A 250V



### Main

Range of product	Standard Series
Product brand	Clipsal

### Complementary

[In] rated current	10 A
[Ue] rated operational voltage	230 V 50/60 Hz conforming to EN 60309-2
Colour	White electric
Material	Plastic
Connections - terminals	Screw terminal
Plug, socket, control station shape	Straight
Duration	6 h

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4 cm
Package 1 Width	10 cm
Package 1 Length	18 cm
Package 1 Weight	37.9 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	108 cm
Package 2 Width	108 cm
Package 2 Length	146 cm
Package 2 Weight	0.426 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	7200
Package 3 Height	118 cm
Package 3 Width	120 cm
Package 3 Length	100 cm
Package 3 Weight	322.216 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>