

Product data sheet

Characteristics

439SHDUA-TR

Plug Top, Standard Series, Flexible, 3 PIN, 10A, Heavy Duty, Unassembled



Main

Range of product	Standard Series
Product brand	Clipsal




Complementary

[In] rated current	10 A
[Ue] rated operational voltage	230 V 50/60 Hz conforming to EN 60309-2
Colour	Transparent
Material	Plastic
Connections - terminals	Screw terminal
Plug, socket, control station shape	Straight
Duration	6 h

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.9 cm
Package 1 Width	3.9 cm
Package 1 Length	10.0 cm
Package 1 Weight	32.1 g
Unit Type of Package 2	CAR
Number of Units in Package 2	200
Package 2 Height	225 mm
Package 2 Width	360 mm
Package 2 Length	465 mm
Package 2 Weight	7 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

