

Product data sheet

Characteristics

49M-VW

Clipsal Iconic, Switch Mechanism, 3-Position Toggle 250V, 10A



Main

| | |
|---------------------------|-----------------|
| Range | Clipsal Iconic |
| Product or component type | Switch |
| Device application | Lighting |
| Load type | LEDi lamp 100 W |
| Colour tint | Vivid white |
| Quantity per set | Set of 20 |

Complementary

| | |
|--------------------------------|----------------|
| Device presentation | Mechanism |
| Control type | Rocker |
| Switch function | 3 positions |
| Marking | ON-OFF-ON |
| Rated current | 10 A |
| [Ue] rated operational voltage | 250 V |
| Connections - terminals | Screw terminal |
| Height | 23 mm |
| Width | 23 mm |
| Depth | 32 mm |
| Net weight | 0.016 kg |

Packing Units

| | |
|------------------------------|--------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 3.2 cm |
| Package 1 Width | 4.5 cm |
| Package 1 Length | 5.9 cm |
| Package 1 Weight | 20 g |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End Of Life Information |