

## Product data sheet

### Characteristics

# 4CB340/10

## Miniature circuit breaker, MAX4, 3P, 40 A, C curve, 10000 A, 415 V



### Main

Product brand	Clipsal
---------------	---------

### Complementary

Curve code	C
Number of poles	3
[In] rated current	40 A
Number of modules	3
[Ue] rated operational voltage	415 V
Breaking capacity	10 kA conforming to EN 60898
Network type	AC
Network frequency	50/60 Hz
[Ui] rated insulation voltage	500 V
Mechanical durability	20000 cycles
Electrical durability	10000 cycles
Connections - terminals	Screw terminal for 1 cable(s) 0.5...35 mm <sup>2</sup> rigid Screw terminal for 1 cable(s) 0.5...25 mm <sup>2</sup> flexible Screw terminal for 1 cable(s) 0.5...25 mm <sup>2</sup> flexible with ferrule
Wire stripping length	13 mm
Tightening torque	3.5 N.m

### Environment

IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Standards	AS/NZS 60898
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C
Height	81 mm
Width	54 mm
Depth	78.5 mm
Net weight	310 g

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.4 cm
Package 1 Width	5.3 cm
Package 1 Length	8.5 cm
Package 1 Weight	0.36 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Halogen content performance	Halogen free plastic parts & cables product