

Product data sheet

Characteristics

4CNT2/2NC

Contacteur, MAX4, 25 A, 240 VAC, 50 Hz, 2 NO + 2 NC



Main

Product brand	Clipsal
Range of product	Series 4 Power





Complementary

[Us] rated supply voltage	415 V AC 50 Hz
Network type	AC
Auxiliary contact composition	2 NC 2 NO

Packing Units

Unit Type of Package 1	PCE
Package 1 Length	12.0 cm
Number of Units in Package 1	1
Package 1 Width	11.0 cm
Package 1 Height	4.0 cm
Package 1 Weight	240.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.