

Product data sheet

Characteristics

4PSO10

Socket outlet, Clipsal - Max 4, DIN Mounted 10 A 250 V 3 pin 2.5 module single pole



Main

Range of product	Series 4
Product brand	Clipsal




Complementary

Number of poles	1
Mounting support	DIN rail
[In] rated current	10 A
[Ue] rated operational voltage	230 V 50/60 Hz conforming to EN 60309-2
Voltage colour	Blue
Duration	6 h
Socket number	1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.4 cm
Package 1 Width	5.1 cm
Package 1 Length	8.9 cm
Package 1 Weight	116.0 g

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Circularity Profile	No need of specific recycling operations

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.