

## Product data sheet

### Characteristics

# 4PSO10D

Clipsal MAX4, Socket outlet DIN Mounted 10 A  
250 V 3 pin 2.5 module double pole



### Main

Range of product	Series 4
Product brand	Clipsal


### Complementary

Number of poles	2
Mounting support	DIN rail
[In] rated current	10 A
[Ue] rated operational voltage	230 V 50/60 Hz conforming to EN 60309-2
Voltage colour	Blue
Duration	6 h
Socket number	1

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.3 cm
Package 1 Width	9.2 cm
Package 1 Length	7.8 cm
Package 1 Weight	122.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	40
Package 2 Height	25.0 cm
Package 2 Width	21.4 cm
Package 2 Length	33.8 cm
Package 2 Weight	4.88 kg

### Offer Sustainability

EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 Yes