

Product data sheet

Characteristics

4PSO20D

Clipsal MAX4 Socket outlet DIN Mounted 20 A
250 V 3 pin 2.5 module double pole



Main

Range of product	Series 4
Product brand	Clipsal




Complementary

Number of poles	2
Mounting support	DIN rail
[In] rated current	20 A
[Ue] rated operational voltage	230 V 50/60 Hz conforming to EN 60309-2
Voltage colour	Blue
Duration	6 h
Socket number	1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.0 cm
Package 1 Width	5.0 cm
Package 1 Length	7.5 cm
Package 1 Weight	120.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	40
Package 2 Height	25.0 cm
Package 2 Width	21.4 cm
Package 2 Length	33.8 cm
Package 2 Weight	40.0 kg

Offer Sustainability

EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes