


Product data sheet

Characteristics

4PSW240

Switch disconnecter, MAX4, 2P, 40 A, 415 V



Main

Range of product	Series 4
Product brand	Clipsal

Complementary

Product or component type	Switch disconnecter
[Ue] rated operational voltage	<= 415 V AC
[In] rated current	40 A
Number of poles	2
Mounting support	DIN rail

Environment

IP degree of protection	Front face: IP20
-------------------------	------------------

Packing Units

Package 1 Weight	151.000 g
Package 1 Height	75.000 mm
Package 1 width	80.000 mm
Package 1 Length	35.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.