

Product data sheet

Characteristics

4RC440SIS300

Residual current circuit breaker, MAX4, 4P, 40 A, 300 mA, type A-SI, 415 V



Main

| | |
|--------------------------------|---|
| Range | MAX4 |
| Product or component type | Residual current circuit breaker (RCCB) |
| Product brand | Clipsal |
| Poles description | 4P |
| Number of modules | 4 |
| [In] rated current | 40 A |
| Earth-leakage sensitivity | 300 mA |
| Earth-leakage protection class | Type A-SI (Super Immunised) |

Complementary

| | |
|--|---|
| [Ue] rated operational voltage | 415 V AC |
| [Uimp] rated impulse withstand voltage | 6 kV |
| Mounting support | DIN rail |
| Size | 81 x 72 x 75 mm conforming to DIN 43880 |
| Trip unit protection functions | Selective protection |

Environment

| | |
|---------------------------------------|--------------|
| Standards | AS/NZS 61008 |
| IP degree of protection | IP40 |
| Pollution degree | 2 |
| Ambient air temperature for operation | -5...40 °C |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 0.35 kg |
| Package 1 Height | 9.2 cm |
| Package 1 width | 7.7 cm |
| Package 1 Length | 8.4 cm |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 1 |
| Package 2 Weight | 1.1 kg |
| Package 2 Height | 9 cm |
| Package 2 width | 11 cm |
| Package 2 Length | 26 cm |
| Unit Type of Package 3 | S03 |
| Number of Units in Package 3 | 27 |
| Package 3 Weight | 9.937 kg |
| Package 3 Height | 30 cm |
| Package 3 width | 30 cm |
| Package 3 Length | 40 cm |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |