

Product data sheet

Characteristics

4RCBE206/10S

Clipsal MAX4, RCBO SLIM 1PN 6A C curve
10mA Type A 6000A



Main

Range	MAX4
Product or component type	Residual current breaker with overcurrent protection (RCBO)
Product brand	Clipsal
Device application	Distribution
Poles description	1P + N
Neutral position	Left
Number of modules	1
Number of protected poles	1
[In] rated current	6 A
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Earth-leakage sensitivity	10 mA
Earth-leakage protection class	Type A
Breaking capacity	6000 A

Complementary

[Ue] rated operational voltage	240 V AC
Local signalling	ON/OFF indication
Mounting mode	Clip-on
Mounting support	DIN rail





Environment

IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
-------------------------	--

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.02 cm
Package 1 Width	0.074 cm
Package 1 Length	0.1 cm
Package 1 Weight	0.141 kg

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile