

Product data sheet

Characteristics

4RCBE210S110

Residual current breaker with overcurrent protection (RCBO), MAX4, 1P + N, 10 A, C curve, 6000 A, 110 V, 30 mA, A type



Main

Range	MAX4
Product or component type	Residual current breaker with overcurrent protection (RCBO)
Product brand	Clipsal
Device application	Distribution
Poles description	1P + N
Neutral position	Left
Number of modules	1
Number of protected poles	1
[In] rated current	10 A
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Earth-leakage sensitivity	30 mA
Earth-leakage protection class	Type A
Breaking capacity	6000 A

Complementary

[Ue] rated operational voltage	110 V AC
Local signalling	ON/OFF indication
Mounting mode	Clip-on
Mounting support	DIN rail

Environment

IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
-------------------------	----------------------------------------------------------------------------------

Packing Units

Package 1 Weight	0.130 kg
Package 1 Height	0.020 mm
Package 1 width	0.075 mm
Package 1 Length	0.100 mm

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile