

Product data sheet

Characteristics

4RCBE220/10S

Residual current breaker with overcurrent protection (RCBO), MAX4, 1P + N, 20 A, C curve, 6000 A, 240 V, 10 mA, A type



Main

Range	MAX4
Product or component type	Residual current breaker with overcurrent protection (RCBO)
Product brand	Clipsal
Device application	Distribution
Poles description	1P + N
Neutral position	Left
Number of modules	1
Number of protected poles	1
[In] rated current	20 A
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Earth-leakage sensitivity	10 mA
Earth-leakage protection class	Type A
Breaking capacity	6000 A

Complementary

[Ue] rated operational voltage	240 V AC
Local signalling	ON/OFF indication
Mounting mode	Clip-on
Mounting support	DIN rail




Environment

IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
-------------------------	--

Packing Units

Package 1 Weight	0.130 kg
Package 1 Height	0.074 mm
Package 1 width	0.074 mm
Package 1 Length	0.098 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation

 [China RoHS Declaration](#)

Environmental Disclosure

 [Product Environmental Profile](#)
