

## Product data sheet

### Characteristics

# 4RCBE225/10S

Residual current breaker with overcurrent protection (RCBO), MAX4, 1P + N, 25 A, C curve, 6000 A, 240 V, 10 mA, A type



### Main

Range	MAX4
Product or component type	Residual current breaker with overcurrent protection (RCBO)
Product brand	Clipsal
Device application	Distribution
Poles description	1P + N
Neutral position	Left
Number of modules	1
Number of protected poles	1
[In] rated current	25 A
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Earth-leakage sensitivity	10 mA
Earth-leakage protection class	Type A
Breaking capacity	6000 A

### Complementary

[Ue] rated operational voltage	240 V AC
Local signalling	ON/OFF indication
Mounting mode	Clip-on
Mounting support	DIN rail




### Environment

IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
-------------------------	--

### Packing Units

Package 1 Weight	0.130 kg
Package 1 Height	0.020 mm
Package 1 width	0.076 mm
Package 1 Length	0.100 mm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>

---

China RoHS Regulation

 [China RoHS Declaration](#)

---

Environmental Disclosure

 [Product Environmental Profile](#)

---