

## Product data sheet

### Characteristics

# 4RCBM232/30

Residual current breaker with overcurrent protection (RCBO), MAX4, 2P, 32 A, C curve, 6000 A, 240 V, 30 mA, AC type



### Main

Range	MAX4
Product or component type	Residual current breaker with overcurrent protection (RCBO)
Product brand	Clipsal
Poles description	2P
Number of modules	2
[In] rated current	32 A
Curve code	C
Earth-leakage sensitivity	30 mA
Earth-leakage protection class	Type AC
Breaking capacity	6000 A

### Complementary

[Ue] rated operational voltage	240 V AC
[Uimp] rated impulse withstand voltage	4 kV
Size	81 x 36 x 77.5 mm conforming to DIN 43880

### Environment

Standards	AS/NZS 61009
IP degree of protection	IP20 IP40
Ambient air temperature for operation	-5...40 °C

### Packing Units

Package 1 Weight	239.000 g
Package 1 Height	40.000 mm
Package 1 width	82.000 mm
Package 1 Length	100.000 mm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Halogen content performance	Halogen free plastic parts product