

Product data sheet

Characteristics

4RCBM240SI30

Clipsal MAX4, RCBO 2 module 2P 40 A C
curve 30mA Type A-SI 6000A



Main

Range	MAX4
Product or component type	Residual current breaker with overcurrent protection (RCBO)
Product brand	Clipsal
Poles description	2P
Number of modules	2
[In] rated current	40 A
Curve code	C
Earth-leakage sensitivity	30 mA
Earth-leakage protection class	Type A-SI (Super Immunised)
Breaking capacity	6000 A

Complementary

[Ue] rated operational voltage	240 V AC
[Uimp] rated impulse withstand voltage	4 kV
Size	81 x 36 x 77.5 mm conforming to DIN 43880

Environment

Standards	AS/NZS 61009
IP degree of protection	IP20 IP40
Ambient air temperature for operation	-25...40 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	8.6 cm
Package 1 Length	10.0 cm
Package 1 Weight	0.25 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free plastic parts product