

Product data sheet

Characteristics

4SSO15D15

Clipsal MAX4 Switched Socket outlet DIN Mounted 1 Gang 15 A 250 V 3 pin 4 module double pole



Main

Range of product	Series 4
Product brand	Clipsal
Device application	Power supply

Complementary

Number of poles	3
Number of modules	2
Number of power socket outlets	1 protective cover
[In] rated current	15 A
[Ue] rated operational voltage	250 V AC

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	5.6 cm
Package 1 Width	8.5 cm
Package 1 Length	7.3 cm
Package 1 Weight	103.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	40
Package 2 Height	25.0 cm
Package 2 Width	21.4 cm
Package 2 Length	33.8 cm
Package 2 Weight	4.12 kg

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------