

Product data sheet

Characteristics

4SSO25D

Socket outlet, MAX4, 10 A, 250 V, 3 pin, 8 module, double pole



Main

Product brand	Clipsal
Device application	Power supply

Complementary

Number of poles	3
Number of modules	2
Number of power socket outlets	2 protective cover
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	196 g
Package 1 Height	60 mm
Package 1 width	75 mm
Package 1 Length	150 mm

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.