

Product data sheet

Characteristics

4SSO25D15

Clipsal MAX4, Switched Socket outlet DIN Mounted 2 Gang 15 A 250 V 3 pin 8 module double pole



Main

| | |
|--------------------|--------------|
| Range of product | Series 4 |
| Product brand | Clipsal |
| Device application | Power supply |

Complementary

| | |
|--------------------------------|--------------------|
| Number of poles | 3 |
| Number of modules | 2 |
| Number of power socket outlets | 2 protective cover |
| [In] rated current | 15 A |
| [Ue] rated operational voltage | 250 V AC |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 0.240 kg |

Offer Sustainability

| | |
|-------------------|---------------------|
| EU RoHS Directive | Under investigation |
|-------------------|---------------------|

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.