

Product data sheet

Characteristics

5031NMMIRL

C-Bus Control and Management System, Mechanism Wall Switches, IR Capable Master Mechanism



Main

Range of product	Series 30M
Product brand	Clipsal
Product or component type	IR capable master mechanism

Complementary

Range compatibility	C-Bus
Device mounting	Wall mounted by Series 30M grid
[Ue] rated operational voltage	15...36 V DC
Input impedance	100 kOhm at 1 kHz
Local signalling	LED (blue/orange) for status
Suitable cable type	Twisted unshielded pairs cable category 5e
Isolation voltage	3.75 kV from C-Bus to mains
Communication network type	C-Bus

Environment




Relative humidity	10...95 % non-condensing
-------------------	--------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.8 cm
Package 1 Width	6.4 cm
Package 1 Length	10 cm
Package 1 Weight	54 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration

RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information