

## Product data sheet

### Characteristics

# 5031NMMIRL

## C-Bus Mechanism Wall Switches, IR Capable Master Mechanism



### Main

Range of product	Series 30M
Product brand	Clipsal
Product or component type	IR capable master mechanism

### Complementary

Range compatibility	C-Bus
Device mounting	Wall mounted by Series 30M grid
[Ue] rated operational voltage	15...36 V DC
Input impedance	100 kOhm at 1 kHz
Local signalling	LED (blue/orange) for status
Suitable cable type	Twisted unshielded pairs cable category 5e
Isolation voltage	3.75 kV from C-Bus to mains
Communication network type	C-Bus

### Environment

Relative humidity	10...95 % non-condensing
-------------------	--------------------------

### Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	2.8 cm
Package 1 Width	6.4 cm
Package 1 Length	10 cm
Package 1 Weight	54 g
Unit Type of Package 2	Gyári csomagolás
Number of Units in Package 2	20
Package 2 Height	104 cm
Package 2 Width	132 cm
Package 2 Length	292 cm
Package 2 Weight	1.162 kg
Package 3 Height	99 cm

### Offer Sustainability

EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Circularity Profile	 <a href="#">End Of Life Information</a>