

Product data sheet

Characteristics

5031PEWP-GY

C-Bus Control and Management System,
Light Level Sensor, 40 - 1600lux, 180deg,
Weatherproof



Main

Range	C-Bus
Product brand	Clipsal
Colour	Grey

Complementary

[Us] rated supply voltage	15...36 V DC
Network type	DC
Colour code	GY




Environment


Ambient air temperature for operation	0...50 °C
---------------------------------------	-----------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	11.5 cm
Package 1 Length	11.8 cm
Package 1 Weight	333.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Height	11.7 cm
Package 2 Width	25.0 cm
Package 2 Length	31.0 cm
Package 2 Weight	2.72 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins