

## Product data sheet

### Characteristics

# 5041NMML

## 40 Series Master Module



### Main

Range	C-Bus
Product brand	Clipsal
Product name	Series 40M
Product or component type	Push-button interface
Device application	Control
Colour	Transparent green
Switch application	Load switching Dimming up/down control Timer Scene control Bell switch Shutter control Fan speed control Blind control

### Complementary

Range compatibility	C-Bus Iconic wall plate Pro Series wall plate
Dimmer control	255 possible levels
Device mounting	Wall mounted by Series 40M grid
[Ue] rated operational voltage	15...36 V DC
Input impedance	100 kOhm at 1 kHz
Local signalling	LED (red/blue) for status
Suitable cable type	Twisted unshielded pairs cable category 5e
Isolation voltage	3.75 kV from C-Bus to mains
Communication network type	C-Bus
Module type	Master
Control type	Push-button
Depth	36 mm
Width	22.8 mm
Height	22.8 mm
Net weight	0.013 kg
Material	Plastic
Starting time	5 s
Module configuration	Programmed with learn mode Programmed with C-Bus software
Time delay range	1s...18h12m15s
Current consumption	18 mA

### Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 % non-condensing
Product certifications	RCM
Standards	AS/NZS CISPR 15 AS/NZS CISPR 14-1 AS/NZS 60669.2.1

## Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	2.7 cm
Package 1 Width	2.7 cm
Package 1 Length	5 cm
Package 1 Weight	55 g
Unit Type of Package 2	Gyári csomagolás
Number of Units in Package 2	20
Package 2 Height	108 cm
Package 2 Width	130 cm
Package 2 Length	290 cm
Package 2 Weight	0.98 kg
Package 3 Height	99 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>