

Product data sheet

Characteristics

5041NMML

Push button interface, C-Bus, 40 Series main module



Main

Range	C-Bus
Product brand	Clipsal
Product name	Series 40M
Product or component type	Push-button interface
Device application	Control
Module type	Main
Colour	Transparent green
Switch application	Load switching Dimming up/down control Timer Scene control Bell switch Shutter control Fan speed control Blind control

Complementary

Range compatibility	C-Bus Iconic wall plate Pro Series wall plate
Dimmer control	255 possible levels
Device mounting	Wall mounted by Series 40M grid
[Ue] rated operational voltage	15...36 V DC
Input impedance	100 kOhm at 1 kHz
Local signalling	LED (red/blue) for status
Suitable cable type	Twisted unshielded pairs cable category 5e
Isolation voltage	3.75 kV from C-Bus to mains
Communication network type	C-Bus
Control type	Push-button
Depth	36 mm
Width	22.8 mm
Height	22.8 mm
Net weight	0.013 kg
Material	Plastic
Starting time	5 s
Module configuration	Programmed with learn mode Programmed with C-Bus software
Time delay range	1s...18h12m15s
Current consumption	18 mA

Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 % non-condensing

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information