

Product data sheet

Characteristics

5055DL-WE

NEO 5GANG KEY INPUT- BK/BA



Main

Product brand	Clipsal
Device presentation	Basic element
Colour	White electric
Dimmer type	Universal

Complementary

Control type	Infrared and button Timer Button Switch
[Ue] rated operational voltage	15...36 V DC
[In] rated current	22 A
Mounting support	Wall
Colour code	WE

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	211.5 g
Package 1 Height	7.8 cm
Package 1 width	11.4 cm
Package 1 Length	15.8 cm

Offer Sustainability

EU RoHS Directive	Not compliant
Circularity Profile	 End Of Life Information