

Product data sheet

Characteristics

5102RVF

RELAY C-BUS 2 CHANNEL 10A



Main

Range	C-Bus
Product brand	Clipsal

Complementary

[Us] rated supply voltage	15...36 V DC
Network type	AC/DC
Connector type	Screw terminals
Width	198 mm
Height	39 mm
Depth	42 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	350 g
Package 1 Height	4.5 cm
Package 1 width	4.5 cm
Package 1 Length	20 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	1.837 kg
Package 2 Height	9.5 cm
Package 2 width	14 cm
Package 2 Length	23.5 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	25
Package 3 Weight	9.187 kg
Package 3 Height	29.5 cm
Package 3 width	31.5 cm
Package 3 Length	33 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins