

## Product data sheet

### Characteristics

# 5502CDGP230

Clipsal C-Bus, DALI-2 Gateway, SpaceLogic C-Bus, 6DIN



### Main

Range	SpaceLogic C-Bus
Product brand	Schneider Electric
Product name	DALI-2 gateway
Product or component type	Gateway
Device application	Light control
Colour	White

### Complementary

Communication port protocol	C-Bus DALI-2
Module configuration	Programmed with C-Bus software
Software name	SpaceLogic C-Bus Commission
Input voltage	110...240 V AC at 50/60 Hz
Supply maximum power	13 W
Guaranteed current	0.23 A
Maximum current	0.25 A
Communication network type	C-Bus DALI
Connector type	2 RJ45
Connections - terminals	Screw terminals
Total number of 18 mm modules	6
Mounting support	DIN rail
Width	108 mm
Height	93 mm
Depth	63 mm

### Environment

Ambient air temperature for operation	-5...45 °C
Ambient air temperature for storage	-20...80 °C
Product certifications	RCM[RETURN]CE

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.8 cm
Package 1 Width	11.1 cm
Package 1 Length	15.6 cm
Package 1 Weight	0.359 kg
Unit Type of Package 2	CAR

Number of Units in Package 2	10
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	4.15 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins