

Product data sheet

Characteristics

56/01/1-GY

Computer Surface Module, Clipsal - 56 Series, IP66, Computer accessory to Suit DB25 Connector



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product or component type	Socket-outlet
Device application	Power supply
Colour	Grey
Product brand	Clipsal
Plug, socket category	Low voltage
Quantity per set	Set of 1
Cover type	Full cover plate
Outlet standard	Industrial
Market segment	Utility Industry Small commercial

Complementary

Colour code	GY
Material	Polycarbonate: cover
Tightening torque	0.8 N.m
Marking	Without marking
Local signalling	Without light indicator
Device mounting	Surface
Fixing mode	By screws
Depth	77 mm
Width	107 mm
Height	107 mm
Net weight	0.001 kg
Targeted country	Australia

Environment

Ambient air temperature for operation	-25...75 °C
---------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.7 cm
Package 1 Width	10.7 cm
Package 1 Length	7.7 cm
Package 1 Weight	0.001 kg

Offer Sustainability

EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes